



RoHS ✓



The information/details in this datasheet merely contain general descriptions or performance factors which, when applied in an actual situation, do not always correspond with the described form, and may be amended by way of the further development of products. The desired performance factors shall only be binding if these are expressly agreed on conclusion of the contract.



Product description

Description	protective cover
Type	CA 00 SD 1
Order No	831-530-400
Color housing	black

Materials

Cover	PA 6 GF
Gasket(s)	NBR
Threaded ring	PA 66 GF

Environmental conditions

Protection class (IEC 60529) *	IP65; IP67
Temperature range	-40°C to +90°C

Accessories

Mating connectors / fitting to	.
	934-124-100: CA 3 LS, cable plug
	934-126-100: CA 6 LS, cable plug angeled

product overview

Article-No.	Type
831-530-400	CA 00 SD 1