



RoHS ✓



The information/details in this datasheet merely contain general descriptions or performance factors which, when applied in an actual situation, do not always correspond with the described form, and may be amended by way of the further development of products. The desired performance factors shall only be binding if these are expressly agreed on conclusion of the contract.



Product description

Description	multi socket straight
Type	MAK 40
Order No	930-150-..., see standard products
Type of contacts	female
Number of contacts	4
Conductor size	max. 0,34 mm ²
Standard	pin assignment: EN 60 130-09 IEC-31
Color housing	see standard products
Color contact bearer	black

Technical data

Rated voltage	34V AC/DC
Rated current *	4A
Pollution degree	3 acc. to DIN EN 60664-1 (VDE 0110-1)
Type of connection	solder
Mating cycles	50 cycles
Suitable cables	max Ø5,5 mm

* Notice derating

Materials

Contact	CuZn
Contact plating	Cu/Sn
Contact bearer	PA 66
Housing	PE LD

Environmental conditions

Protection class (IEC 60529) *	IP30
Temperature range	-20°C to +60°C, notice Derating


* only if mounted and locked in combination with Hirschmann / Lumberg connector.

Flammability class

Contact bearer	UL 94 V-2
----------------	-----------

Notes

Do not connect / disconnect under load.



product overview

Article-No.	Type	Color housing
930-150-500	MAK 40 schwarz	schwarz / black
930-150-517	MAK 40	grau / grey