




TRIAx

connecting the future



LTE 16 Way IR Pass Amplifier

Article number: 334026

Product description:

- Distributes to multiple TV's around the home
- Allows control of Sky Digital receivers when used with Triax Digital Links
- 2 Input 16 Output
- Short circuit protected on each output
- Power on LED
- Screened housing
- F-Connectors
- Easy to mount fixing
- Mains powered
- 9VDC/15mA on outputs

Specifications

ORDER INFORMATION	
EAN Number	5702663340268
CHARACTERISTICS	
Output level IMD 2/IMD 3 @ 60 dB	93.0 dB μ V
Return Path	5...30 MHz
FREQUENCY	
Frequency range DAB	217-230 MHz

Frequency range FM	87.5-108 MHz
Frequency range	87.5-230 / 470-790 MHz
Output frequency range	85...790 MHz
Frequency range UHF	470-790 MHz
Frequency range BIII/DAB	85...230 MHz
GAIN	
Gain	10 +/-2 dB
Noise figure	<5 dB
ELECTRICAL	
Impedance	75 Ω
OPERATIONAL	
LED indicator	Yes
AC Supply voltage	230 \pm 10% / 50Hz VAC
CONNECTORS	
Connector Type	F-female
Number of inputs	2
Number of outputs	16
MECHANICAL	
Colour	RAL 7016
Packing QTY	1
Net Weight	0,785 kg
Tara Weight	0,140 kg
Total Weight	0,925 kg
Remarks	Fully screened within plastic housing >25dB rejection at 821MHz Short circuit protection on outputs