



TRIAx

connecting the future



LTE W2 - Splitter

Article number: 370564

Product description:

Wolsey LTE Outdoor Splitter

- 1 Input 2 Outputs
- Bi-Directional Through Line Power
- Power Pass on All Outputs
- F-Connectors
- Weatherproof Housing
- Fully Screened Enclosure

Specifications

ORDER INFORMATION	
EAN Number	5702663705647
CHARACTERISTICS	
Type.	Splitter
FREQUENCY	
Band	VHF / UHF
LTE protection	800
Input 1 - frequency	47...790 MHz

Input 1 - band	VHF / UHF
Input 1 - channels	2...60
GAIN	
Input 1 - gain	<4.0 dB
LOSS	
Rejection @ 821 MHz (LTE D6)	>25.0 dB
RETURN LOSS	
Return Loss	10 Typ dB
OPERATIONAL	
DC Passthrough	Yes (12VDC / 400mA)
CONNECTORS	
Number of inputs	1
Number of outputs	2
Connector Type	F-female
MECHANICAL	
Colour	Black
Packaging Volume	0,001 m3
Net Weight	0,200 kg
Tara Weight	0,035 kg
Total Weight	0,235 kg
Remarks	Full screened DC pass to all Outputs, Bi-directional DC Pass - 12V/400mA Max