



Quality Products. Service Excellence.

15 & 20 Amp Vertical Outlet Strips *1588-9-JV Series*

With Shielded Cord and Toolless Mounting Option



Features

- Low-profile slim design.
- Constructed of rugged light weight aluminum.
- Designed for a variety of applications, specifically where electromagnetic or radio frequency interference is a concern:
 - Install in your server cabinets
 - Wall mount cabinets
 - Open frame racks
 - Or install horizontally above your work bench.
- Shielded cord reduces EMI/ RFI and "dirty" power from utilities.
- Shielding is by way of 100% coverage in aluminum mylar foil with a 20 gauge drain wire.
- Each outlet strip included a hardware mounting kit. Order P/N: **1585CLIP** for additional hardware kit.
- Includes toolless PDU button mounting provision.
- Receptacles are 1" square and are equally spaced over the length of the power strip.
- With on/off switch and 15 or 20 Amp circuit breaker.

Specifications

- Heavy duty cord, either 12 gauge (12/3 SJT) or 14 gauge (14/3 SJT) wire for extreme temperature ranges and integral molded plug.
- Plug types for 15 Amp models are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Plug types for 20 Amp models are NEMA 5-20P straight blade or NEMA L5-20P locking type.
- Rated 15 or 20 amps, 120 volts.
- UL/cUL Listed Standard UL1363 file No. E166039 & CSA C22.2 No. 308-14 & CSA C22.2 No. 0.4-04
- NOTE #1: Outlet strips can NOT be used between the front & rear panel rails of rack cabinets as they (and the equipment plugs) will interfere with mounted equipment and mounted accessories.
- NOTE #2: To properly use on rack cabinets, allow sufficient depth BEHIND the rear panel rails for vertically mounting to the cabinet.

Toolless button PDU mounting provision shown



Four models each with a different plug type.



15A straight blade.



15A twist lock



20A straight blade.



20A twist lock

Part Number	Current Rating	Length	Number of Outlets	Cord Length	Shielded Cord	Color	NEMA Plug Type	Plug Style
1588H12B1JV	15A	77.00	12	15	Yes	Natural	5-15P	Straight Blade
1588H12D1JV	15A	77.00	12	15	Yes	Natural	L5-15P	Locking
1589H77G1JV	20A	77.00	12	15	Yes	Natural	5-20P	Straight Blade
1589H77D1JV	20A	77.00	12	15	Yes	Natural	L5-20P	Locking

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.