




Inside of fitting



**16 AMP ELECTRONIC OUTDOOR TIME DELAY SWITCH**

- ABS construction
- Multiple accurate time settings using dip switches and rotary adjuster
- Incandescent 16 Amp max, fluorescent 6 Amp max, compact fluorescent 3 Amp max (maximum six fluorescent lights), low voltage 3 Amp max & fans and ventilation equipment 3 Amp max
- Multi point switching, connect two or more units in parallel
- Multi range delay function from 2 seconds to 2 hours: reduces energy consumption

• M.O.M: 1 / O.P.Q: 50

Code	Colour	IP Rating
TLS68EX	Grey	IP66

SWITCH SETTING				TIMER FUNCTION
1	2	3	4	
0	0	1	0	2 seconds to 50 seconds
1	0	1	0	50 seconds to 20 minutes
1	1	1	0	20 minutes to 70 minutes
1	1	0	0	70 minutes to 2 hours
-	-	-	1	Timer function disabled

