

Product information

18V Impact Wrench LXT



DTW190Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Driving Shank	1/2" Square
Impacts	0-3,000 ipm
Standard Bolt	M8-M16
High Tensile Bolt	M8-M12
Noise sound pressure	94 dB(A)
Noise sound power	105 dB(A)
Noise K factor	3 dB(A)
No Load Speed	0 - 2,300 rpm
Max Fastening Torque	190 Nm
Vibration: Fastening Bolt	8.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Net weight	1.4 - 1.8 kg



- Electric brake
- Variable speed control trigger.
- Forward/reverse rotation
- LED job light
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Ergonomically designed handle with rubberised soft grip fits your hand perfectly to provide maximum control and comfort.

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com