

Product information

18V Combi Drill



Satisfying the professional's needs

HP457DWE10

Battery Type	Lithium-ion
Battery Type	G-Series
Voltage	18 v
Battery Quantity (1.3Ah)	2
Charging Time	60 min
Max. in masonry	13 mm
Max. in steel	13 mm
Max. in wood	36 mm
Blows per Minute (Hi) - ipm	0 - 21,000 ipm
Blows per Minute (Lo) - ipm	0 - 6,000 ipm
No Load Speed (Hi)	0 - 1,400 rpm
No Load Speed (Lo)	0 - 400 rpm
Max Torque S/H	24 / 42 Nm
Noise sound pressure	81 dB(A)
Noise sound power	92 dB(A)
Noise K factor	3 dB(A)
Vibration: Impact drilling into concrete	7.0 m/sec ²
Vibration: Drilling into metal	2.5 m/sec ²
Vibration K factor	1.5 m/sec ²
Net weight	1.7 kg



- Includes 74 Piece Accessory Set
- Variable speed control by trigger
- Forward/reverse rotation
- Electric brake
- 2 mechanical gears.
- Keyless Chuck
- 16 Torque Settings
- Ergonomic soft grip

Details correct as of: 2-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com