

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Multistep Drills
Catalogue number	3008, 3009, 3010
Date	03/11/2008

Range Description Multistep Drills				
Features <ul style="list-style-type: none"> Centres, drill and de burrs sheet metal in one operation HSS construction Self starting tip Dual flute construction for less drilling pressure, faster drilling and longer tool life Three flats on drive shaft for secure drive in drill chucks 				
Item Number	Item Description	EAN No	Commodity code	Carton Qty
T3008	HSS-Multistepdrill 6, 9, 12.5, 15.2, 18.6, 20.4, 22.5, 25.5, 28.3 & 30.5mm (PG7, PG9, PG11, PG13, PG16, M25, PG21)	5013969985283	82075060	1
T3009	HSS-Multistepdrill 4, 5, 6, 7, 8, 9, 10, 11 & 12mm Diameters	5013969985290	82075060	1
T3010 1	HSS-Multistepdrill 4, 6, 8, 10, 12, 14, 16, 18 & 20mm Diameters	5013969985313	82075060	1
T3010 2	HSS-Multistepdrill 6, 8, 10, 12, 14, 16, 18, 20, 22, 24, 26, 28 & 30mm Diameters	5013969985320	82075060	1

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not

	covered
Country of origin	Germany

Dimensional details

	Product only				Product on primary packaging			
Item	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T3008	31	31	95	146	35	35	115	164
T3009	12	12	65	18	25	25	105	30
T3010 1	20	20	70	50	25	25	105	62
T3010 2	30	30	95	146	35	35	115	164

	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
Item	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T3008	-	-	-	-		
T3009	-	-	-	-		
T3010 1	-	-	-	-		
T3010 2	-	-	-	-		

Packaging waste details

	Primary Packaging				Secondary packaging			
Item	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T3008	18	Box			-	-	-	-
T3009	10	Box			-	-	-	-
T3010 1	12	Box			-	-	-	-
T3010 2	18	Box			-	-	-	-