

Top of fitting



CR10




CR10PW



PLUG IN CEILING ROSE

- Urea construction
- 6 Amp rating 4 terminal
- Shrouded plug terminals and cord grip: complies with 2.2kg load test
- 4 terminals as standard offering extra live connection: ideal for emergency auxiliary use
- BESA box mounting



CR10PW

- Pre-wired with 2 metres of heat resistant 4 core flex: time saving, easy installation

- **CR10** = M.O.M: 10 / O.P.Q: 180
- **CR10PW** = M.O.M: 10 / O.P.Q: 60

Code	Version	Colour	IP Rating
CR10	Un-wired	White	IP20
CR10PW	Pre-wired		