



Einhell

EXPERT

Multifunctional Tool

TE-MG 200 CE

Item No.: 4465040

Ident No.: 11055

Bar Code: 4006825577204

The TE-MG 200 CE multifunction tool is a high-quality, compact and ergonomic helper for experts on extension and renovation jobs, which with its many different options saves a great deal of effort. Sawing, sanding, scraping and much more besides are performed easily and speedily with this handy all-rounder. The electronic speed control ensures smooth starting and enables the power to be adjusted exactly to the particular task.

Features & Benefits

- Constant speed electronics for maximum precision
- Constant electronic system - no speed loss under load
- Safe and pleasant working thanks to the soft grip
- Soft start
- Ultra-slim design for optimal handling
- Tool chuck (adjustable to 12 settings)
- Cable clip
- Triangular grinding/sanding plate
- 6x grinding/sanding paper (3*P60/3*P120)
- Dust extraction device can be mounted without tools
- Scraper
- Plunge-cut saw blade for wood
- Practical dust extraction adapter
- Allen key
- Delivery in convenient transport and storage case




Technical Data

- Mains supply	230 V 50 Hz
- Power	200 W
- Oscillating speed	30000 - 42000 min ⁻¹
- Angle of oscillation	3 °
- Sandpaper size	93 x 93 x 93 mm

Logistic Data

- Product weight	1.05 kg
- Gross weight single packaging	2.74 kg
- Dimensions single packaging	361 x 110 x 272 mm
- Pieces per export carton	5 Pieces
- Gross weight export carton	15.6 kg
- Dimensions export carton	580 x 375 x 300 mm
- Container quantity (20"/40"/40"HC)	2150 4450 5225



Available as special accessories



Starter-Kit, 6 pcs.
Multifunctional Tool Accessory
Item No.: 4465010
Bar Code: 4006825553178
Einhell Grey



Fliesen-Set
Multifunctional Tool Accessory
Item No.: 4465017
Bar Code: 4006825625523
Einhell Accessory



Boden- und Einbau-Set
Multifunctional Tool Accessory
Item No.: 4465016
Bar Code: 4006825625516
Einhell Accessory