


Material number	0 603 3A0 070
EAN	3165140526876
** Further purchase only in set of 5	✓
1 saw blade T 144 D 2 608 630 040	✓
Plastic case	✓
Voltage	230.0 V
Top seller	0.0



## Technical data

### Technical data

Power input	500 W
Power output	300 W
Stroke rate at no load	500 – 3.100 spm
Sole plate	Steel
Machine weight	1,7 kg



### Cutting depth

Cutting depth in wood	70 mm
Cutting depth in steel	4 mm

### Functions

Bosch SDS	✓
Bosch Low Vibration	✓
Bosch Electronic	✓
Dust blowing function	✓
Softgrip	✓

### Noise/vibration information

Sound pressure level	88 dB(A)
Sound power level	99 dB(A)
Uncertainty K	3 dB

## Sales information

---

### Positioning

- The Easy Jigsaw PST 700 E from Bosch: Easy Rider – for precise curves and straight lines

### User benefit

- As easy as can be: compact size, low weight and outstanding handling ensure perfect control and optimum user comfort
- Precision in every material due to the tried-and-tested Bosch Electronic: stroke rate control using the trigger switch for an easy sawing start and material-specific working
- Minimal vibrations and safe and convenient working due to Bosch “Low Vibration” with linear mass balance and ergonomic softgrip

### Other features

- Powerful 500 W motor and 70 mm cutting depth in wood – making even hard jobs easy
- Bosch SDS ensures effortless and safe saw blade changes within seconds – without the need for additional tools
- Switchable air blast function ensures a clear view of the cutting line at all times
- Adjustment of the sole plate for mitre cuts up to 45°
- Dust extraction port – for dust-free working
- Robust sole plate for steady guidance
- New cable guide with hanging hook for practical storage