

0 601 513 060 – GST 150 BCE

Material number	0 601 513 060	0 601 513 070
EAN	3165140463621	3165140463638
1 x jigsaw blade T 144 DP, Precision for Wood available separately as set of 3: 2 608 633 A31	✓	✓
Anti-splinter guard 2 601 016 096	✓	✓
Dust extraction set 2 605 510 294	✓	✓
Glide shoe spare part number 2 601 099 183	✓	✓
Hood spare part number 2 605 510 293	✓	✓
Suction nozzle spare part number 2 605 730 055	✓	✓
Voltage 110 V	✓	
Voltage 240 V		✓
Packaging dimensions (width x length x height)	355 x 390 x 115 mm	360 x 385 x 110 mm
Voltage, electrical	110.0 V	240.0 V



Technical data

Technical data

Rated input power	780 W
Stroke rate at no load	500 – 3.100 spm
Weight	2,7 kg
Cable length	4 m

Cutting depth


Cutting depth in wood	150 mm
Cutting depth in aluminium	20 mm
Cutting depth in non-alloyed steel	10 mm

Noise/vibration information

Sound pressure level	83 dB(A)
Sound power level	94 dB(A)
Uncertainty K	3 dB

Linked products

Dust Special system components	✓
--------------------------------	---



Sales information

Positioning

- The most powerful tool in its price class

User benefit incl. Reason to believe

- High power reserves, even in hard and thick beams, due to powerful and overload-capable 780-watt motor
- Extremely robust and bend-resistant sole plate for the toughest jobs
- High cutting precision due to new saw blade clamping system