

Material number	0 603 3A7 070
EAN	3165140606585
* Further purchase only in set of 2	✓
1 saw blade for wood S 2345 X 2 609 256 704	✓
Voltage	230.0 V
Top seller	0.0



Technical data

Technical data

Power input	710 W
Cutting depth in wood	150 mm
Cutting depth in steel	10 mm
Saw blade stroke	20 mm
Machine weight	3,0 kg



Functions

Bosch SDS	✓
Softgrip	✓

Noise/vibration information

Sound pressure level	86 dB(A)
Sound power level	97 dB(A)
Uncertainty K	3 dB

Sales information

Positioning

- The Sabre Saw PSA 700 E – cuts effortlessly through thick and thin

User benefit

- Saws any material – whether wood-cutting blades, metal-cutting blades or flexible bi-metal blades – all standard saw blades fit the PSA 700 E
- Very comfortable to use due to modern sabre saw design, optimum size-to-weight ratio, ergonomic softgrip and optimum switch arrangement
- Powerful 710 watt motor – very high power, even for the toughest jobs when you are renovating, converting rooms and working in the garden

Other features

- Always with the right power for the material you are working on – start sawing softly and then speed up
- Bosch SDS – for effortless saw blade changing in seconds – without the need for additional tools
- Totally robust – quality workmanship and robust housing
- Bow design handle – for safe handling and easy working

