



## DWE305PK

### 1100 Watt - Reciprocating Saw

#### Selling Proposition

- 1100 Watt motor designed for heavy duty applications
- 4 position blade clamp allows for flush cutting and increased versatility
- With a 29 mm stroke length, the DWE305PK delivers excellent cutting performance
- Lever-action keyless blade clamp for quick and easy blade changing
- Ideal for plumbers, electricians, heating, HVAC , and builders

#### Standard Equipment

- Heavy duty carrying case

#### Warranty Specifications

- 1 Year Free Service Contract
- 1 year full warranty
- 30 Day No Risk Satisfaction Guarantee

Specifications	
Power Input	1100 Watts
No Load Stroke Rate	0-2800 spm
Stroke Length	29 mm
Max. Cutting Capacity [Wood]	280 mm
Max. Cutting Capacity [Steel Sections & Pipes]	100 mm
Max. Cutting Capacity [PVC]	130 mm
Weight	3.5 kg
Length	435 mm