

Product information

18V RECIPROCATING SAW



Satisfying the professional's needs

DJR183Z

Battery Type	Lithium-ion
Body only machine	1
Voltage	18 v
Capacity in Wood	50 mm
Capacity in Mild Steel Pipe	50 mm
Strokes per Minute	0 - 3000 spm
Stroke Length	13 mm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	7 m/sec ²
Vibration: Cutting Chipboard	8 m/sec ²
Net weight	1.5 - 1.7 kg



- Single LED job light with pre-glow function
- Shoe Adjustment
- Tool less blade clamp for reciprocating saw blade. Simply turn to remove the blade.
- Two switch levers with variable speed control; Trigger switch on tool handle & Paddle switch on tool body to make operation easier at any grip position for versatile applications by using either trigger.
- Rubberized soft grip provides comfortable and sure grip.

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com