

Product information

165mm Circular Saw



HS6601

Depth of Cut @ 90°	54.5 mm
Blade Diameter	165 mm
Depth of Cut @ 45°	37.5 mm
Bore Diameter	20 mm
Noise sound pressure	87 dB(A)
Noise sound power	98 dB(A)
Noise K factor	3 dB(A)
Input Wattage	1050 w
No Load Speed	5200 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Wood	2.5 m/sec ²
Net weight	3.4 kg



STANDARD EQUIPMENT: Dust nozzle, Rip fence (Guide rule), TCT saw blade, Hex wrench

- Compact & Lightweight
- Ergonomic soft grip
- Rear dust exhaust port
- Rear angular guide for smooth and precise adjustment of bevel angle
- Single action lever for quick adjustment of cutting depth
- Aluminium die-cast safety cover
- Aluminium base plate
- Aluminium die-cast blade casing
- Flat motor housing end
- Compatible with Guide Rail

Details correct as of: 9-7-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com