

DHS710ZJ

| | |
|-------------------------|------------------------|
| Battery Type | Lithium-ion |
| Voltage | 36 (18V x2) v |
| Blade Diameter | 190 mm |
| Max Cut @ 0° | 66 mm |
| Max Cut @ 45° | 49 mm |
| Max Cut @ 50° | 44 mm |
| Bore (B) | 20 mm |
| No Load Speed | 4600 rpm |
| Vibration K factor | 1.5 m/sec ² |
| Vibration: Cutting Wood | 2.5 m/sec ² |
| Net weight | 3.9 - 4.6 kg |



STANDARD EQUIPMENT: 821552-6 MAKPAC CONNECTOR CASE (TYPE 4), 837861-3 MAKPAC INLAY FOT TYPE 4 CASE, TCT saw blade, Hex wrench, Rip fence (Guide rule), Dust nozzle

- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Compact and lightweight design.
- Rear dust exhaust port
- Same depth of cut as HS7100.
- Durable but lightweight magnesium die-cast blade case and safety cover.
- Blower function to clear wood dust from cutting line.