

Socket Set 1/4 " + 1/2", S103



Product description

Heavy duty steel alloy, matt.
ISO 1174 / DIN 3120

Article number: S103

Packing Quantity: 1pc.

Contents 1/4 ":

- 12 hex sockets: 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 6 hexagon inserts, long version: 7, 8, 9, 10, 11, 13 mm
- 1 extension 100 mm
- 1 Universal Joint
- 1 Plug-in handle with 2-component handle
- 1 Slim Ratchet with 72 teeth and 5 ° backward tilt angle with a quick release button

Contents 1/2 ":

- 17 hex inserts: 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 20, 21, 24, 27, 30, 32, 34 mm
- 6 hexagon inserts, long version: 10, 13, 16, 17, 18, 19 mm
- 2 extensions 125 mm and 250 mm
- 1 articulated handle 250 mm
- 1 Universal handle
- 2 spark plug Sockets 16 mm (5/8 ") and 21 mm (13/16")
- 1 Slim Ratchet with 72 teeth and 5 ° backward tilt angle with a quick release button
- 1 bit ratchet with 48 teeth

Additional accessories:

- 1 bit holder 1/4 "
- 3 1/4 bits "PH 1, 2, 3, 3 1/4 bits" PZ 1, 2, 3, 6 bits 1/4 "Hex 3, 4, 5, 6, 7, 8 mm
- 9 bits 1/4 "Torx T6, T8, T9, T10, T15, T20, T25, T30, T40
- 1 bit holder 1/2 " - 5/16"
- 3 5/16 "bits Torx T45, T50, T55
- 1 connection part 1/4 "
- 1 Adapter 1/4 "13 combination wrenches 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm
- 9 Angle Screwdriver Set: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10
- 1 removable lid separation, available as a knee pad