

Piezo Buzzer - 41.P11T240A-LF



■ PZ Buzzer Single 24VDC PLT ABS SP

■ Colour - Black




General Specification

Model Number	41.P11T240A-LF
Operating Voltage Range (VDC)	1.0 ~ 28.0
Rated Voltage (VDC)	24
Max. Rated Current * (mA)	15
Min. Sound Output* (dBA/ 30cm)	95
Frequency * (Hz)	2900 ± 500
Tone Nature	Single
Operating Temperature (°C)	-20 ~ + 60
Terminal	Plate
Housing Material	ABS
Weight (g)	35


* Value applying at rated voltage

Dimension (mm)

TOP VIEW



SIDE VIEW



BOTTOM VIEW

