



ECM-200

Order No.: 23.0280

Price upon request

PRODUCTINFOS

PA desktop microphone,

with gooseneck.

- Electret, omnidirectional polar pattern
- Push-to-talk button and lock button

TECHNICAL SPECIFICATIONS

ECM-200

Type	desktop microphone
Transmission method	cable
Polar pattern	omnidir.
System	electret
Audio frequency range	60-12,000 Hz

ECM-200

Nominal impedance	1 k Ω
Sensitivity	6 mV/Pa
S/N ratio	> 40 dB
Power supply	1 x 1.5 V batt. AA size
Admiss. ambient temp.	0-40 °C
Dimensions	75 x 25 x 110 mm (console housing), 200 mm (length of gooseneck)
Weight	298 g
Connection	6.3 mm plug