



## PDM-300

Order No.: 23.1200

**Price upon request**

### PRODUCTINFOS

**PA desktop microphone,**

with gooseneck.

- Dynamic, cardioid polar pattern
- Low-noise push-to-talk switch, latching or non-latching
- 1 m helix cable, balanced, with 6.3 mm mono plug

### TECHNICAL SPECIFICATIONS

#### PDM-300

Type	desktop microphone
Transmission method	cable
Polar pattern	cardioid
System	dynamic

**PDM-300**

Audio frequency range	60-12,000 Hz
Nominal impedance	600 $\Omega$
Sensitivity	3.2 mV/Pa
Admiss. ambient temp.	0-40 °C
Dimensions	120 x 60 x 160 mm (console housing) 310 mm (length of gooseneck)
Weight	810 g
Cable	1 m
Connection	6.3 mm plug