

MKS-34/SW - 2way Speaker Cabinet



Pairs of 2-way speaker systems, 30 W, 4 Ohm

- Dome tweeter
- Excellent sound quality
- Black (SW) or white (WS) plastic cabinet
- Movable mounting bracket
- Bevelled shape of cabinets also allows mounting in corners



Technical Data

Music power	: 45 W _{MAX}
Power rating	: 30 W _{RMS}
Max. frequency range	: 80-20,000 Hz
Impedance	: 4 Ohm
SPL (1 W/1 m)	: 87 dB
Max. rated SPL	: 101 dB
Dimensions	: 130x192x115 mm
Weight	: 1.3 kg
Connections	: spring-load. speaker term.
Mounting facility	: for wall hooks
System	: