

CR-S048/060VADC1SS



Products → Low Voltage Products and Systems → Control Products → Electronic Relays and Controls
→ Interface Relays and Optocouplers

General Information

Extended Product Type:	CR-S048/060VADC1SS
Product ID:	1SVR405521R5100
EAN:	4013614499227
Catalog Description:	CR-S048/060VADC1SS Socket 1c/o, A1-A2=48-60VAC/DC, 250VAC
Long Description:	CR-S048/060VADC1SS Socket 1c/o, A1-A2=48-60VAC/DC, 250VAC screw terminals

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	2CDC117022D0201
Instructions and Manuals:	2CDC117022D0201

Dimensions

Product Net Width:	6.3 mm
Product Net Height:	76.4 mm
Product Net Depth / Length:	88.5 mm
Product Net Weight:	0.025 kg

Technical

Function:	Accessory for interface relays CR-S
Sub-Function:	Socket
Rated Control Supply Voltage (U_s):	48 ... 60 V AC/DC
Terminal Type:	Screw Terminals

Environmental

Ambient Air Temperature:	Operation -40 ... +70 °C Storage 0 ... +40 °C
RoHS Status:	Following EU Directive 2011/65/EU

Technical UL/CSA

Connecting Capacity UL/CSA:	Flexible 14 AWG Rigid 14 AWG
Tightening Torque UL/CSA:	4.42 in·lb

Certificates and Declarations (Document Number)

CSA Certificate:	CSA_262671-2785566
cURus Certificate:	cURus508_E244328
Declaration of Conformity - CE:	1SVD982017-0001
EAC Certificate:	EAC_RU_C-PL.ME77.B.01873
Environmental Information:	1SAA981009-2403
Instructions and Manuals:	2CDC117022D0201
RoHS Information:	1SVD982017-0001
VDE Certificate:	VDE_40039479

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	93 mm
Package Level 1 Height:	81 mm
Package Level 1 Depth / Length:	66 mm
Package Level 1 Gross Weight:	0.26 kg
Package Level 1 EAN:	4013614486357

Classifications

Object Classification Code:	K
E-nummer:	4001394
ETIM 4:	EC001456 - Relay socket
ETIM 5:	EC001456 - Relay socket
ETIM 6:	EC001456 - Relay socket
ETIM 7:	EC001456 - Relay socket
eClass:	7.0 27371603
UNSPSC:	39121516

