

OVR SLTN



OVR SLTN Surge Protective Device



General Information

Extended Product Type	OVR SLTN
Product ID	7TCA085400R0323
EAN	5415022374452
Catalog Description	OVR SLTN Surge Protective Device
Long Description	OVR SLTN SLIM LINE DATA SPD FOR TWISTED PAIR TELEPHONE LINES

Ordering

EAN	5415022374452
Minimum Order Quantity	1 piece
Customs Tariff Number	8536308000

Dimensions

Product Net Width	106.5 mm
Product Net Height	104.6 mm
Product Net Depth / Length	7 mm
Product Net Weight	0.08 kg

Container Information

Package Level 1 Units	1 piece
Package Level 1 EAN	5415022374452

Environmental

Ambient Air Temperature	Operation -40 ... +80 °C
-------------------------	--------------------------

Additional Information

Connection Type	Screw clamp
Discharge Current	I (max, 8 / 20 μ s) 10 kA
Maximum Continuous Operating Voltage (U _c)	296 V
Number of Protected Poles	3
Product Main Type	Data SPD

Product Name	Surge Protective Devices
Rated Current (I_n)	750 mA
Rated Frequency (f)	20 MHz
Standards	IEC 61643-21
Suitable For	To protect systems against transient overvoltages or surges from lightning and electrical switching events
Voltage Protection Level (Up)	298 V
Wire Stripping Length	9.5 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	9AKK106713A8157
Declaration of Conformity - CE	9AKK106713A8383
Instructions and Manuals	9AKK106713A8726

Classifications

ETIM 4	EC000941 - Surge protection device for power supply systems
ETIM 5	EC000941 - Surge protection device for power supply systems
ETIM 6	EC000943 - Surge protection device for data networks/MCR-technology

Categories

Low Voltage Products and Systems → Surge Protective Devices → IEC/EN standard → ABB OVR telecoms & computer line protection

