

**SAK Series  
AD 4 EN**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	AD 4 EN
Order No.	<a href="#">0375600000</a>
Version	SAK Series, cover plate, Yellow, 24.1 mm
GTIN (EAN)	4008190517663
Qty.	10 pc(s).

## Data sheet

### SAK Series AD 4 EN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Width	24.1 mm	Width (inches)	0.949 inch
Height	20 mm	Height (inches)	0.787 inch
Depth	1 mm	Depth (inches)	0.039 inch
Net weight	0.7 g		

### Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

### Material data

Material	PVC	Colour	Yellow
----------	-----	--------	--------

### System specifications

Version	End and intermediate plate	Mounting rail	none
---------	----------------------------	---------------	------

### Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

### Classifications

ETIM 3.0	EC000886	ETIM 4.0	EC000886
ETIM 5.0	EC000886	ETIM 6.0	EC002848
eClass 6.2	27-14-11-33	eClass 7.1	27-14-11-33
eClass 8.1	27-14-11-33	eClass 9.0	27-14-11-33
eClass 9.1	27-14-11-92		

### Approvals

ROHS	Conform
------	---------