

**TERMSERIES
ZQV 1.5N/R6.4/19 BL**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



TERMSERIES accessories include:

- Spare relay
- Base
- Partition plates
- Cross-connections
- Power-feed modules

General ordering data

Type	ZQV 1.5N/R6.4/19 BL
Order No.	1391620000
Version	TERMSERIES, Cross-connector
GTIN (EAN)	4050118191813
Qty.	10 pc(s).

Data sheet

**TERMSERIES
ZQV 1.5N/R6.4/19 BL**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	119 mm	Width (inches)	4.685 inch
Height	13.1 mm	Height (inches)	0.516 inch
Depth	4.9 mm	Depth (inches)	0.193 inch
Net weight	4.65 g		

Temperatures

Operating temperature, max.	60 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-40 °C
Operating temperature	-40 °C...60 °C	Storage temperature	-40 °C...85 °C

Cross-connection data

Rated voltage	250 V	Rated current	17.5 A
Insulation	Yes	Electric shock protection	Yes
Colour	Blue	No. of cross-connected terminals	19
Pitch in mm (P)	6.4 mm	Type of mounting	Plugged
Version	can be cut to length		

General data

Version	can be cut to length	Colour	Blue
UL 94 flammability rating	V-0		

Insulation coordination

Rated voltage	250 V
---------------	-------

Connection data

Pitch in mm (P)	6.4 mm
-----------------	--------

Rated data UL

Rated current (UL)	10 A
--------------------	------

Classifications

ETIM 3.0	EC000489	ETIM 5.0	EC000489
ETIM 6.0	EC002586	eClass 6.2	27-14-11-40
eClass 7.1	27-37-92-08	eClass 8.1	27-37-92-08
eClass 9.0	27-37-16-92	eClass 9.1	27-37-16-92

Approvals

Approvals



ROHS Conform

Data sheet**TERMSERIES**
ZQV 1.5N/R6.4/19 BL**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Downloads**

Brochure/Catalogue	CAT 4.2 ELECTR 18/19 EN
Engineering Data	EPLAN, WSCAD
User Documentation	Operating Instructions

Data sheet

TERMSERIES
ZQV 1.5N/R6.4/19 BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Dimensional drawing

