

**Industrial Ethernet  
IE-BS-V04P-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



PushPull plug-in connector set according to IEC  
61076-3-106 ver.4 (IEC24702), plastic with RJ45 insert

**General ordering data**

Type	IE-BS-V04P-RJ45-C
Order No.	<a href="#">1963490000</a>
Version	Flange RJ45, IP67, Version 4, coupling, Cat.6 <sub>A</sub> / Class E <sub>A</sub> (ISO/IEC 11801 2010)
GTIN (EAN)	4032248645589
Qty.	10 pc(s).

**Industrial Ethernet  
IE-BS-V04P-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Net weight 39.8 g

**Temperatures**

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Operating temperature	-40 °C...70 °C	Storage temperature	
Installation temperature			

**General data**

Connection 1	RJ45	Connection 2	RJ45
Description of article	Version 4, coupling	Seal material	NBR
Housing main material		Category	Cat.6A / Class E <sub>A</sub> (ISO/IEC 11801 2010)
Contact surface	PA UL 94 V0	Shielding	360° all-round enclosure
Protection degree	Gold over nickel	Plugging cycles	750
	IP67		

**Standards**

Connector standard	IEC 61076-3-106 Var. 4, IEC 60603-7-51	Certificate no. (cULus)	E316369
--------------------	---	-------------------------	---------

**Downloads**

Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class E Category 6, 3 connector permanent link	ac107534.pdf	Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class E Category 6, 4 connector channel	ac107533.pdf
Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class EA Category 6A, 2 connector channel	ac107535.pdf	Attestation of conformity ISO/IEC EN & TIA/EIA Screened Class EA Category 6A, 4 connector channel	z1755b-07-D.pdf
GOST Approval	POCC DE.ME25.B01411.pdf	UL Approval	DUXR.E316369.pdf

**Classifications**

ETIM 3.0	EC001121	ETIM 4.0	EC000437
ETIM 5.0	EC000437	ETIM 6.0	EC001121
UNSPSC	30-21-18-17	eClass 5.1	27-26-12-03
eClass 6.2	27-26-12-03	eClass 7.1	27-25-05-04
eClass 8.1	19-17-01-25	eClass 9.0	19-17-01-25
eClass 9.1	27-44-09-90		

**Product information**

Descriptive text accessories Plug inserts can also be ordered separately. Refer to Inserts.

**Approvals**

Approvals




ROHS Conform

**Industrial Ethernet  
IE-BS-V04P-RJ45-C**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Drawings**

**Installation cut-out**



Mounting cut-out: 1. With central screw connection / 2. For mounting with four M3 screws