

PRO-SIGNAL



PSG3035

2 PORT HDMI SWITCH SPLITTER

IMPORTANT SAFETY INFORMATION

Please read these instructions carefully before use and retain for future reference.

OVERVIEW

- This device can connect and switch two HDMI sources to two HD displays.
- Either input can be switched to both displays simultaneously.
- Can be used with DVD, Blue-Ray DVD, STB, HD Player, PS3, PS4, XBOX, PC etc.

WHAT'S IN THE BOX

- Main unit.
- USB power supply cable.
- User's Manual.

INSTALLATION

- Please make sure all devices you wish to connect have been powered off.
- Connect two source devices to the switcher inputs using appropriate HDMI cables.
- Connect both the outputs to two display using appropriate HDMI cables.
- Connect the USB DC 5V power cable to the converter and to a device with a suitably equipped USB power socket.
- The power LED lights when the power is applied and the device is switched on.
- Pressing the SWITCH button on the input panel with switch between the two connected input HDMI sources.

SPECIFICATIONS

| | |
|-----------------------|--|
| Operating environment | -10 to 55° / Storage -20 to 60°, Humidity up to 90% |
| Power supply | USB |
| Power requirement | 5V DC 500mA |
| HDMI Input | 4K/30Hz,1080P/1080I/720P/576P/480P/60Hz |
| HDMI Audio support | DTS-HD/Dolby-trueHD/LPCM 2/5.1/7.1CH/DTS/Dolby-AC3/DSD |
| Input video signal | 0.5~1.5Volts p-p |
| Output DDC signal | 5 Volts p-p (TT1L) |
| Max baud rate | 9.0Gbps |
| Max bandwidth | 300MHz |
| Dimensions | 70 x 60.5 x 20.5mm |
| Weight (not inc PSU) | 110g |



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP
Man Rev 1.0