

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1462160001](#)
Status: **Active**
Overview: [Antennas](#)
Description: RHCP LDS SMT GPS Antenna

Documents:

3D Model	Packaging Specification PK-146216-001-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-146216-001-001 (PDF)	Product Literature (PDF)
Application Specification AS-146216-001-001 (PDF)	

General

Product Family	Antennas
Series	146216
Component Type	Surface Mount Device Antenna
Overview	Antennas
Product Literature Order No	987651-5071
Product Name	RHCP LDS GPS Antenna
Protocol	GPS
Type	GPS Antenna
UPC	889056690140

Physical

Cable Length	N/A
Length	11.80mm
Mounting Style	Surface Mount
Net Weight	0.655/g
Packaging Type	Embossed Tape on Reel
Polarization	Right Handed Circular
Radiation Pattern	Omnidirectional
Thickness	5.95mm
Width	11.50mm


Electrical

Band#1 F_End (MHz)	1566
Band#1 F_Start (MHz)	1556
Band#2 F_End (MHz)	1580
Band#2 F_Start (MHz)	1571
Band#3 F_End (MHz)	1607
Band#3 F_Start (MHz)	1597
Electrical Connectivity	SMD
Peak Gain (dBi)	0.6 @ 1561M, 1.1 @ 1575M, 1.1 @ 1602M
Return Loss - S11 (dB)	< -10
Total Efficiency	>55% @ 1561M, >57% @ 1575M, >60% @ 1602M

Material Info

Reference - Drawing Numbers

Application Specification	AS-146216-001-001
Packaging Specification	PK-146216-001-001
Product Specification	PS-146216-001-001
Sales Drawing	SD-146216-001-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[146216 Series](#)