



PA-900

Order No.: 17.1190

Price upon request

PRODUCTINFOS

Mono PA mixing amplifier

- 1 x 120 W
- Silent operation due to fanless cooling concept
- 4 balanced mic/line inputs
- Mic 1 with priority circuit and automatic talkover
- Additional connection for desktop microphone via screw terminal
- 1 aux input
- Speaker outputs via screw terminals
- Line output
- Insert facility, e.g. for effect units, equalizers, feedback controllers
- Input and output level controls
- 2-way tone control for the output
- 20 V phantom power for each microphone input, can be selected individually
- Mains operation or 24 V emergency power operation
- Removable mounting brackets

TECHNICAL SPECIFICATIONS

PA-900

Channels	5
Power rating	120 W

PA-900

Power rating at 4 Ω	120 W
Power rating at 100 V	120 W
Peak music power output (P_{MAX})	160 W
Output impedance	4 Ω
Inputs	3 mV (mic), 200 mV (line), 140 mV (aux)
Frequency range	50-15,000 Hz, ± 3 dB
Equalizer bass	± 10 dB/100 Hz
Equalizer treble	± 10 dB/10 kHz
S/N ratio	> 80 dB
THD	< 0.5%
Power supply	~ 230 V/50 Hz/300 VA, DC 24 V/9 A
Mains voltage	~ 230 V
Mains frequency	50 Hz
Power consumption, operation	300 VA
Operating voltage (possible alternative)	DC 24 V
Power supply (possible alternative)	DC 9 A
Admiss. ambient temp.	0-40 $^{\circ}$ C
Dimensions	482 x 88 x 275 mm, 2 RS
Width	482 mm
Height	88 mm
Depth	275 mm
Rack spaces, RS	2
Weight	9.9 kg
Connections	4 x XLR (mic/line), 1 x RCA L/R (aux), screw terminals (speakers)