



MPX-4PA

Order No.: 20.2070

Price upon request

PRODUCTINFOS

3-zone mixer

- 3 zones with user-defined routing of all input channels
- XLR and RCA zone outputs
- 6 input channels (4 stereo ways, 2 microphone ways)
- Both microphone ways can only be routed together
- Recessed gain control for each input channel
- Microphone ways, each with 2-way tone control, talkover and PAD switch
- Stereo channels, switchable 2 x phono/line and 2 x line/line
- Zone outputs, each with 3-way equalizer, LED level display of the stereo master, balance control, pre-fader listening (PFL) and mono/stereo selector switch
- Adjustable headphone output with pre-fader listening (PFL) to the stereo input channels and zone outputs
- Connection for gooseneck light GNL-204

TECHNICAL SPECIFICATIONS

MPX-4PA

No. of channels	6
No. of inputs	12
Mic input	1.5 mV, 2 x 6.3 mm jack
Line input	150 mV, 5 x RCA L/R
CD input	150 mV, 1 x RCA L/R
Phono input	3 mV, 2 x RCA L/R
Master output	1 V/600 Ω , 3 x 3-pole XLR L/R, 3 x RCA L/R
Headphones	$\geq 8 \Omega$, 1 x 6.3 mm jack
Gooseneck lamp	12 V/0.75 W, 1 x BNC
Frequency range	20-20,000 Hz
THD	0.1%
S/N ratio	61 dB, unweighted
Equalizer bass	+12 dB, -12 dB/50 Hz
Equalizer midrange	+12 dB, -12 dB/1 kHz
Equalizer treble	+12 dB, -12 dB/10 kHz
Talkover	-16 dB
Power supply	\sim 230 V/50 Hz/20 VA
Mains voltage	\sim 230 V
Mains frequency	50 Hz
Power consumption, operation	20 VA
Admiss. ambient temp.	0-40 $^{\circ}$ C
Width	482 mm
Height	177 mm
Depth	105 mm
Rack spaces, RS	4
Weight	4 kg