



## MPX-44/SW

Order No.: 20.2420

**Price upon request**

### PRODUCTINFOS

#### **6-channel stereo DJ mixer,**

with black brushed aluminium front panel.

- 6 input channels (4 stereo ways, 2 microphone ways)
- Stereo input channels, switchable 2 x phono/line and 2 x line/line, with LED level display of the stereo master
- Input channels, each with gain control and 3-way equalizer, stereo input channels with cut function
- DJ mic with automatic talkover, PAD switch and on-air switch
- Mic with PAD switch and on-air switch
- Switches illuminate blue when activated
- Adjustable, crossfader-controlled headphone output with pre-fader listening (PFL) to the stereo input channels and mic
- Replaceable crossfader with assignment switches
- Especially easy-sliding high-quality faders
- Master output with stereo LED level display
- Additional outputs booth and zone
- Connection for gooseneck light GNL-204

## TECHNICAL SPECIFICATIONS

### MPX-44/SW

No. of channels	6
No. of inputs	12
Mic input	1.5 mV, 2 x 6.3 mm jack
Line input	150 mV, 5 x RCA L/R
CD input	150 mV, 1 x RCA L/R
Phono input	3 mV, 2 x RCA L/R
Master output	1 V/600 $\Omega$ , 1 x 3-pole XLR, 1 x RCA L/R
Record output	0.5 V/600 $\Omega$ , 1 x RCA L/R
Monitor output	1 V/600 $\Omega$ (zone), 1 x RCA L/R
Booth output	1 V/600 $\Omega$ , 1 x RCA L/R
Headphones	$\geq 8 \Omega$ , 1 x 6.3 mm jack
Gooseneck lamp	12 V/0.75 W, 1 x BNC
Frequency range	20-20,000 Hz
THD	0.1%
S/N ratio	61 dB, unweighted
Equalizer bass	+12 dB, -12 dB/50 Hz (mic) +15 dB, -30 dB/50 Hz (channels 1-4)
Equalizer midrange	+12 dB, -12 dB/1 kHz (mic) +15 dB, -30 dB/1 kHz (channels 1-4)
Equalizer treble	+12 dB, -12 dB/10 kHz (mic) +15 dB, -30 dB/10 kHz (channels 1-4)
Talkover	-16 dB, automatic
Crossfader	yes
Power supply	$\sim$ 230 V/50 Hz/20 VA
Mains voltage	$\sim$ 230 V
Mains frequency	50 Hz
Power consumption, operation	20 VA
Admiss. ambient temp.	0-40 $^{\circ}$ C
Width	482 mm
Height	177 mm
Depth	105 mm
Rack spaces, RS	4
Weight	3.6 kg