



GNL-304

Order No.: 24.3710

Price upon request

PRODUCTINFOS

LED gooseneck light

- 4 white LEDs of high luminous intensity
- 12 V/60 mA
- Narrow beam angle
- XLR connector, 3 poles
- Length: 41 cm

Suitable for DC voltage and AC voltage due to built-in rectifier.

TECHNICAL SPECIFICATIONS

GNL-304

Type	LED gooseneck light
Type	4 white LEDs
Colour	black

GNL-304

Power supply	12 V/60 mA
Length	41 cm
Weight	90 g
Connections	3-pole XLR
Other features	narrow beam angle
Sales unit	1