


UHD/4K to 1080p up/de-scaler

Instruction Manual



Instructions:

1. Connect the device to the scaler via HDMI cable.
 2. From the scaler to the television connect via HDMI cable.
 3. Plug the scaler in using the power supply supplied.
 4. Finally, press the silver button until the required setting is selected.
- ⇒ For example, if the device from the input is 4K and the output to the television is 1080p ensure the lights are on IN:4K and OUT:1080p.



Technical	
Frequency Bandwidth	594 MHz(18Gbps)
Video Resolutions	Up ot 4K2K@60Hz
Audio Format	Dolby® TrueHD, DTS-HD Master Audio™, and LPCM digital audio streams up to 7.1 channels
ESD Protection	Human body model — ±8kV (air-gap discharge) & ±4kV (contact discharge)
Connections	
Inputs	1x HDMI Type A 1x DC power connector 1x USB Connector 1x Scaling Button
Outputs	1x HDMI Type A
Mechanical	
Housing	Metal Enclosure
Dimensions	80mm [W] x 50mm [D] x 20mm [H]
Net Weight	200g
Power Supply	Input: AC100 - 240V 50/60Hz Output: DC 5V/1A (US/EU standards, CE/FCC/UL certified)
Power Consumption (Max)	3W
Operation Temperature	32 - 104°F / 0 - 40°C
Storage temperature	-4 - 140°F / -20 - 60°C
Relative Humidity	20 - 90% RH (no condensation)