


# 76 01 125


## Diagonal Cutter for electromechanics



- Cutting edges additionally induction hardened, cutting edge hardness approx. 63 HRC
- Lap joint
- Vanadium electric steel, forged, multi stage oil-hardened



<b>Article No.</b>	76 01 125
<b>EAN</b>	4003773018490
<b>Head</b>	polished
<b>Handles</b>	plastic coated
<b>Style</b>	0
<b>Pliers</b>	black atramentized
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	2,3
<b>Cutting capacities hard wire (diameter) Ø mm</b>	1,5
<b>Cutting capacities piano wire (diameter) Ø mm</b>	0,6
<b>Cutting capacities soft wire (diameter) Ø mm</b>	0,4 - 3,0
<b>B mm</b>	16
<b>D mm</b>	9
<b>A mm</b>	14,5
<b>Length mm</b>	125
<b>Net weight g</b>	90



technical change and errors excepted

