


LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Durable PFA Type K & T Exposed Welded Tip Thermocouples



- ◆ Thermocouple types K & T to IEC 584
- ◆ Fast response, welded exposed junction
- ◆ 5 metre long Teflon® PFA insulated twin-twisted lead
- ◆ Durable construction with choice of conductor size, 1/0.315mm solid or 7/0.2mm stranded
- ◆ Miniature plug termination
- ◆ Temperature range -75°C to +250°C
- ◆ Ideal for test & development applications

Thermocouple Type	Conductors Size	Length	Manufactures Part No.
Type K	1/0.315mm	5 m	Z2-K-5.0-MP-1/0.315 PFA TTP+MP
Type K	1/0.315mm	10 m	Z2-K-10.0-MP-1/0.315 PFA TTP+MP
Type T	1/0.315mm	5 m	Z2-T-5.0-MP-1/0.315 PFA TTP+MP
Type T	1/0.315mm	10 m	Z2-T-10.0-MP-1/0.315 PFA TTP+MP
Type K	7/0.2mm	5 m	Z2-K-5.0-MP-7/0.2 PFA TTP+MP
Type K	7/0.2mm	10 m	Z2-K-10.0-MP-7/0.2 PFA TTP+MP
Type T	7/0.2mm	5 m	Z2-T-5.0-MP-7/0.2 PFA TTP+MP
Type T	7/0.2mm	10 M	Z2-T-10.0-MP-7/0.2 PFA TTP+MP

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com