

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.


We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

RTD Extension Cable – 4 core PVC Platinum Resistance Thermometer Extension Cable, PVC insulated & screened



- ◆ PVC insulated cable for extending Platinum Resistance Thermometers
- ◆ Can be used to extend 2, 3 or 4 wire RTD configurations
- ◆ Commonly used for Pt100Ω thermometers but also suitable with other types such as Pt130, Pt500 & Pt1000Ω
- ◆ 4 core PVC insulated 7/0.2mm tin plated copper conductors, twisted cores, polyester tape & nylon cord, tin plated copper braided screen with PVC insulated outer jacket
- ◆ Cores colour coded 2 x Red / 2 x White to IEC-751 with black outer jacket
- ◆ Heat resistant PVC to 105°C
- ◆ Good for general purpose cable, highly flexible & waterproof
- ◆ Insulation rating -10°C to 105°C
- ◆ Supplied in 10 & 25 metre reel lengths

Type	Conductors	mm ²	Cores	Screen	Jacket	Reel Length	Manufacturers Part No.
RTD	7/0.2mm	0.219	x 4	Yes	Black	10 metres	WC-006/10M
RTD	7/0.2mm	0.219	x 4	Yes	Black	25 metres	WC-006/25M

Overall sheath Dimension (approx.)
4 core = 4.4mmØ

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com