

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY



Miniature Quick Wire Panel Mount Socket with Stainless Steel Bracket



'IEC Colour coded'

- Miniature size sockets supplied with stainless steel brackets
- Available in Thermocouple types K, J, T, E, N, R/S, B
- For Types K, J, T, E & N contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220 deg°C

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Part Code
K	Green	+Nickel Chromium	-Nickel Alloy	IM-K-SSPFQ
B	Grey	+Copper	-Copper	IM-B-SSPFQ
E	Violet	+Nickel Chromium	-Copper Nickel	IM-E-SSPFQ
J	Black	+Iron	-Copper Nickel	IM-J-SSPFQ
N	Pink	+Nickel/Chro/Silicon	-Nickel Silicon	IM-N-SSPFQ
R/S	Orange	+Copper	-Copper Alloy	IM-R/S-SSPFQ
T	Brown	+Copper	-Copper Nickel	IM-T-SSPFQ



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email sales@labfacility.com

Website www.labfacility.com