


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	* "A" +/- .06	LEGEND	Total Markers Each Legend per Book	STD. PKG. BOOK (S)	STD. CTN. BOOK (S)	TOTAL PAGES PER BOOK
PCMB-1 PCMBRS-1	0.217	0 THRU 9	45	1	10	10
PCMB-2 PCMBRS-2	0.217	A THRU Z, 0 THRU 15, +, -, /	10	1	10	10
PCMB-3 PCMBRS-3	0.217	1 THRU 45	10	1	10	10
PCMB-4 PCMBRS-4	0.217	1, 2, 3	150	1	10	10
PCMB-5 PCMBRS-5	0.217	A, B, C	150	1	10	10
PCMB-6	0.217	T1, T2, T3	150	1	10	10
PCMB-7	0.217	L1, L2, L3	150	1	10	10
PCMB-8	0.217	1 THRU 15	6	1	10	10
		16 THRU 90	4	1	10	10
PCMB-9	0.217	A THRU Z, +, -, /, 0	2	1	10	10
		1, 2, 3, A, B, C	45	1	10	10
PCMB-10	0.217	L1, L2, L3, T1, T2, T3	30	1	10	10
		Solid NEMA colors red, yellow, white, light blue, light green, black, brown, orange, gray, dark green	45	1	10	10
PCMB-11	0.217	1 THRU 30	15	1	10	10
PCMB-12	0.217	A THRU Z	15	1	10	10
		+	8	1	10	10
		-	7	1	10	10
PCMB-13	0.434	.464 NO LEGEND, Blank (write-on)	21	1	10	10
		+, -, AC, DC	45	1	12	12
		P.N.G.	21			
PCMB-14	0.217	SPARE, BLANK (WRITE-ON)	10	1	10	10
PCMB-15	0.217	46 THRU 90	15	1	10	11
		"0", "+", "-", "1" THRU "45"	10			
PCMB-16	0.217	0 THRU 33, A, B, C, +, -, L1, L2, L3, T1, T2, T3	10	1	10	10
PCMB-25	0.217	0 THRU 9	45	1	10	12
		L1, L2, L3, T1, T2, T3	15	1	10	

NOTE : 1. MILLIMETERS ARE IN [] .

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
5	2/23/15	RVU	CLW	JHAC	GMC4 WAS GMC. ADD PN WITH SUFFIX "S" TO PCMBR. UPDATE ON FORMAT A WITH PANDUIT LOGO AND TOLERANCES.	GAECN02625
4	10/19/11	SHOR	VJS	RAMI	CORRECTED PCMB-15, TOTAL MARKERS FOR "1" THRU "45".	C10607
3	1/19/10	RVU			0.434 WAS 0.295, 0.361, & 0.464. P.N.G. WAS POS, NEG, GND. 21 WAS 33, & 27. 12 WAS 10. FOR PCMB-13 ONLY.	5947
2	11/2/09	RVU			REVISED ON PCMB-15, 15 WAS 10. 11 WAS 10.	5900
1	8/20/09	RVU			UPDATE TABLES, FOLLOW WITH THE CATALOG. TOLERACNES INCORRECT, .12, .062, .025 WAS .03, .015, .010.	5771
0	8/2/07	RVU			DRAWING RELEASE. C10607 R	5099

TITLE
**PCMB-*, PCMBRS-*
BOOK PAGE**
CUSTOMER DRAWING

ITEM REVISION NAME
100414BA/06

DATASET FILE NAME
100414BA_DC_C10607/07E

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]
.x ± .12 [3.05] .xxx ± .025 [.635]
.xx ± .062 [1.57] ANGLES ± 5 °

MATERIAL:
GMC4

DRAWING NUMBER:
C10607

THIRD ANGLE PROJECTION

DRAWN BY: RVU DATE: 8/2/07 CHK: JHAC SCALE: NTS

SHT 1 OF 1 SIZE: A