

03 06 180 T

Combination Pliers with tether attachment point



- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether



Article No.	03 06 180 T
EAN	4003773081395
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Head	
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacity copper cable, multiple-stranded mm²	16
Cutting capacities medium hard wire (diameter) Ø mm	3,4
Cutting capacities hard wire (diameter) Ø mm	2,2
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	12,0
Nominal size	180 mm
Length mm	180
Net weight g	271

technical change and errors excepted