

08 22 145 T

Needle-Nose Combination Pliers with tether attachment point



- Handy use when working in confined areas thanks to slim head design and pointed jaws (anti-twist)
- Gripping surfaces with special convex contour on one side for secure gripping of flat parts
- Milled groove in the gripping area permits small parts such as nails, pins and bolts to be held and pulled
- The reliable and diverse combination pliers when out and about
- Easy cutting thanks to the high leverage joint
- With cutting edges for soft, medium-hard and hard wire
- Long service life and stable tips
- High-grade special tool steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection

Article No.	08 22 145 T
EAN	4003773080640
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Pliers	black atramentized
Cutting capacities medium hard wire (diameter) Ø mm	3,0
Cutting capacities hard wire (diameter) Ø mm	2,0
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	8,0
Cutting capacity copper cable, multiple-stranded mm²	16
Length mm	145
Net weight g	150

technical change and errors excepted