

14 26 160

Diagonal Insulation Stripper



- With long cutter
- High cutting capacity due to high leverage joint
- Precision stripping holes for single (solid) conductors of 1.5 and 2.5 mm²
- Convenient cutting of NYM cables up to 5 x 2.5 mm²
- Long tips for ultra fine cutting work also in confined areas
- Induction hardened precision blades, cutting edge hardness approx. 60 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



Article No.	14 26 160
EAN	4003773040279
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Head	
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	1,5
Cutting capacities soft wire (diameter) Ø mm	2,5
Stripping capacities in square millimetres mm²	1,5 + 2,5
AWG	15 + 13
Length mm	160
Net weight g	216



technical change and errors excepted

