

25 06 160


Snipe Nose Side Cutting Pliers Radio Pliers



- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for medium hard and hard wire
- Cutting edges additionally induction hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



Article No.	25 06 160
EAN	4003773033806
Pliers	chrome plated
Handles	insulated with multi-component grips, VDE-tested
Style	0
Head	
Insulation standard	IEC 60900 DIN EN 60900
Cutting capacities medium hard wire (diameter) Ø mm	2,5
Cutting capacities hard wire (diameter) Ø mm	1,6
T1 mm	9,0
W3 mm	16,5
W4 mm	3,0
T2 mm	2,5
L3 mm	50,0
Nominal size	160 mm
Length mm	160
Net weight g	146



technical change and errors excepted

