




# 26 15 200 T

## Snipe Nose Side Cutting Pliers with tether attachment point with tether attachment point



- Elastic tips: dimensionally stable even when twisted
- Distortion-tolerant, elastic precision tips
- Half-round, long, tapered jaws
- With cutting edges (hardness approx. 61 HRC) for soft, medium-hard and hard wire
- Vanadium electric steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection

<b>Article No.</b>	26 15 200 T
<b>EAN</b>	4003773079996
<b>Pliers</b>	chrome plated
<b>Head</b>	
<b>Handles</b>	with multi-component grips, with integrated tether attachment point for a tool tether
<b>Style</b>	1
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	3,2
<b>Cutting capacities hard wire (diameter) Ø mm</b>	2,2
<b>T1 mm</b>	9,5
<b>W3 mm</b>	18,0
<b>W4 mm</b>	3,0
<b>T2 mm</b>	2,5
<b>L3 mm</b>	73,0
<b>Length mm</b>	200
<b>Net weight g</b>	204



technical change and errors excepted