


35 12 115 ESD

Electronics Pliers ESD



- Precision pliers for fine assembly work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- For gripping, holding and bending
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Soft transitions; no sharp edges
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- With two-colour dual component grips, black/grey
- Ball bearing chrome steel




ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

Article No.	35 12 115 ESD
EAN	4003773024835
Head	mirror polished
Handles	with multi-component grips
Style	1
B mm	22,5
D mm	7
E mm	1,7
F mm	4,0
A mm	11
Nominal size	115 mm
Length mm	115
Net weight g	74



technical change and errors excepted

