

85 01 250

KNIPEX SmartGrip® Water Pump Pliers with automatic adjustment



PATENTED




- Ideal for frequent changeovers to workpieces of different sizes
- Automatic adjustment per one-hand operation both for right-handed and left-handed use
- Good access to the workpiece thanks to the slim dimensions of head and joint area and flush joint bolt
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC: high wear resistance and stable gripping
- Box-joint design for high stability due to double guide
- Guard prevents operators' fingers being pinched
- Locking lever for space saving transport with reliable closed handles
- Chrome vanadium electric steel, forged, multi stage oil-hardened

Adjustment to suit the workpiece is automatic with the KNIPEX SmartGrip®! Place the outer jaw on the workpiece, squeeze the handles - turn!

Article No.	85 01 250
EAN	4003773061304
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Capacity for pipes, inches (diameter) Ø Inch	1 1/4
Capacities for pipes (diameter) Ø mm	32
Capacities for nuts mm	36
Length mm	250
Net weight g	370




Automatic adjustment: no time-consuming trial and error-adjusting to find the correct opening size in case of differently sized workpieces (e.g. the red highlighted nuts and fittings). Everything done with a single grasp.



Locking lever for space saving transport with reliable closed handles



Slim dimensions for good access to the workpiece using one-hand operation



Self-locking on pipes and nuts: no slipping on the workpiece

technical change and errors excepted

