

# 95 12 165 Cable Shears



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- Easy cutting with one-hand operation
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint, self-retaining screw
- High-grade special tool steel, forged, oil-hardened



<b>Article No.</b>	95 12 165
<b>EAN</b>	4003773029182
<b>Tool</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Style</b>	1
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	15
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	50
<b>AWG</b>	1/0
<b>Length mm</b>	165
<b>Net weight g</b>	250

*technical change and errors excepted*

