


# 97 22 240




## Crimping Pliers



- For cutting cables, stripping wire and crimping insulated and non-insulated terminals, connectors and plug type connectors
- With threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- Bolted joint for higher stability and even movement
- Special steel, high-strength



<b>Article No.</b>	97 22 240
<b>EAN</b>	4003773070726
<b>Pliers</b>	black lacquered
<b>Handles</b>	with multi-component grips
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,5 - 6,0
<b>Applications</b>	insulated terminals + cable connectors
<b>Number of crimping positions</b>	3
<b>AWG</b>	20 - 10
<b>Length mm</b>	240
<b>Net weight g</b>	300



technical change and errors excepted

