

97 43 06

Crimp System Pliers for exchangeable crimping dies



PATENTED



- Just one tool for almost 1000 crimping applications
- Almost parallel crimping die movement
- Repetitive, high crimping quality due to precision dies and integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force due to lever action for fatigue-reduced operation
- Ergonomically designed handles
- Different locators for precise positioning of the connectors
- Crimping dies for applications not covered in the range offered here, may be available on request
- Chrome vanadium electric steel in special quality, oil-hardened
- With attached crimping dies for insulated terminals and plug connectors

With the possibility of crimping almost all currently available crimping connections with just one tool and state-of-the-art crimping pliers technology, the crimp system pliers solves almost all tasks in mobile and stationary crimping technology and is an excellent tool for professionals to use for standard crimping.

Article No.	97 43 06
EAN	4003773031048
Pliers	burnished
Handles	with multi-component grips
Applications	Crimp System Pliers for insulated terminals and plug connectors
Capacity in square millimetres mm²	0,5 - 6,0
Number of crimping positions	3
AWG	20 - 10
Length mm	200
Net weight g	610

technical change and errors excepted

